

Jacuzzi J-365

Specifications

Seating Capacity.....	6-7 Adults
Dimensions	84" x 91" x 37.50" (214 cm x 232 cm x 96 cm); For Complete Dimensions, See page 75
Dry Weight.....	805 lbs (365 kg)
Filled Weight (Average Fill)	4,099 lbs (1,859 kg)
Water Capacity (Average Fill).....	395 US gallons (1,495 Liters)
Electronic Controls	Solid state electronic touchscreen controls, programmable temperature, filtration, and heat cycles
Pump 1.....	North America (60 Hz): 1-Speed, 4.8 HP brake, 2.5 HP continuous, 56 Frame
Export (50 Hz):.....	N/A
Pump 2.....	North America (60 Hz): 1-Speed, 4.8 HP brake, 2.5 HP continuous, 56 Frame
Export (50 Hz):.....	N/A
Circulation Pump.....	Yes, 8-Hour
Heater	North America (60 Hz): 5.5kW High Flow
Export (50 Hz)	N/A
Total Jacuzzi® PowerPro® Jets.....	46
Seat A Jets	4 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Large Rotational
Seat B Jets	1 Jacuzzi® PowerPro® FX Large
Seat C Jets	2 Jacuzzi® PowerPro® NX2, 2 Jacuzzi® PowerPro® FX, 3 Jacuzzi® PowerPro® MX
Seat D Jets	1 Jacuzzi® PowerPro® FX Large Rotational
Seat E Jets (Standard model).....	10 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Rotational
Seat E Jets (optional IR Therapy)	8 Jacuzzi® PowerPro® FX, 2 IR Therapy Lights, 2 Jacuzzi® PowerPro® FX Rotational
Seat E HYDROSOOTHE™ Jets.....	2 Jacuzzi® PowerPro® FX Directional with independent flow rate valve
Seat F Jets.....	2 Jacuzzi® PowerPro® NX2, 2 Jacuzzi® PowerPro® FX Rotational, 2 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Large
Footwell (G).....	8 Jacuzzi® PowerPro® FX Mini, 1 Jacuzzi® PowerPro® FX
Massage Selectors	2
Air Controls.....	4, On/Off rocker style
Water Management System.....	Two 60 ft² filter cartridges; filter 1 on 8-hour circulation pump; filter 2 on jets pump 1; Factory installed ClearRay Active Oxygen® System; Optional True Water® System
Export (50 Hz):.....	N/A
LED Lighting	One underwater light with 4 color modes, one colored waterfall light, cup holders, 2 HYDROSOOTHE pillow lights, and exterior lights
ProFinish™ Cabinet Colors.....	Modern Hardwood, Brushed Gray, and Smoked Ebony
Acrylic Colors	Platinum, Silver Pearl, Morning Mist, Midnight, Canyon, Monaco (while quantities last)
Headrests	4
Waterfalls	One independent flow rate (on or off) adjustment; powered by the circulation pump
Heater:	North America (60 Hz): 5.5 kW, High Flow
Export (50 Hz):	N/A
Electrical Requirements:.....	North America (60 Hz): 240 VAC@40A, 50A, or 60A Export (50 Hz): N/A
Warranty*.....	North America (60 Hz): 10 Years Shell, 7 Years Shell Surface, 5 Years Plumbing Component Leaks, 5 Years Equipment and Controls, 5 Years Cabinet, 2 Years Jets, 2 Years Lights, 1 Year Stereo; Export (50 Hz): N/A
Special Features (Standard).....	SmartTub® Module
Special Features (Optional).....	2 IR Therapy Lights
Audio System (Optional).....	BLUEWAVE® Spa Stereo System (Bluetooth/Aux compatible) with four speakers and subwoofer




Shown with the optional
IR Therapy Lights


Jacuzzi J-365

Operation/Seat Depths

Note: Shown with the optional IR Therapy Lights



46 Total Jets



Spa Operation Subject to Change without Notice

Seat Depths

A = 26.50" (67.47 cm)
B = 25.25" (64.14 cm)
C = 25.25" (64.14 cm)
D = 23.75" (60.33 cm)
E = 28.25" (71.76 cm)

F = 27.25" (69.22 cm)
G = 17.50" (44.45 cm)
H = 33.75" (85.73 cm)

Listed dimensions represent distance from top of acrylic to lowest point in seat. Tolerance $\pm 0.5"$ (1.27 cm).




Dimensions/Specifications are Subject to Change Without Notice


Jacuzzi J-365

Dimensions


TOP VIEW



FRONT/BACK VIEW
Tolerance: $\pm 0.5"$ (1.27 cm)



LEFT SIDE VIEW
Tolerance: $\pm 0.5"$ (1.27 cm)




STOP

IMPORTANT! Always measure each hot tub for exact dimensions BEFORE designing its foundational support and/or decking.


STOP

TOP VIEW



Important Panel Details

NOTE: Over time the panel(s) may bow, this is considered normal. The panels will straighten out when reinstalled into the mounting channel. Place one end of the panel into the channel first then flatten the panel and insert the other end.



From the edge of the ABS pan

Dimensions/specifications subject to change without notice. Tolerance $\pm 0.5"$ (1.27 cm)