


Jacuzzi J-385

Specifications


Seating Capacity.....	6-7
Dimensions	91" x 91" x 37.50" (232 cm x 232 cm x 96 cm); For complete dimensions, see page 75
Dry Weight.....	850 lbs (386 kg)
Filled Weight (Average Fill).....	4,686 lbs (2,126 kg)
Water Capacity (Average Fill)	460 US gallons (1,741 Liters)
Electronic Controls	Solid state electronic touchscreen controls, programmable temperature, filtration, and heat cycles
Pump 1.....	North America (60 Hz): 1-Speed, 4.8 HP brake, 2.5 HP continuous, 56 Frame
Export (50 Hz):.....	N/A
Pump 2.....	North America (60 Hz): 1-Speed, 4.8 HP brake, 2.5 HP continuous, 56 Frame
Export (50 Hz):.....	N/A
Circulation Pump.....	Yes, 8-hour
Heater	North America (60 Hz): 5.5kW High Flow
Export (50 Hz)	N/A
Total Jacuzzi® PowerPro® Jets	51
Seat A Jets	4 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Large Rotational
Seat B Jets	1 Jacuzzi® PowerPro® FX Rotational, 2 Jacuzzi® PowerPro® FX Large
Seat C Jets	2 Jacuzzi® PowerPro® NX2, 2 Jacuzzi® PowerPro® FX Rotational, 4 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Large
Seat D Jets	2 Jacuzzi® PowerPro® FX Large Rotational
Seat E Jets (Standard model).....	10 Jacuzzi® PowerPro® FX, 2 Jacuzzi® PowerPro® FX Rotational, 2 Jacuzzi® PowerPro® BX
Seat E Jets (optional IR Therapy)	8 Jacuzzi® PowerPro® FX, 2 IR Therapy Lights, 2 Jacuzzi® PowerPro® FX Rotational, 2 Jacuzzi® PowerPro® BX
Seat E HYDROSOOTHE™ Jets.....	2 Jacuzzi® PowerPro® FX Directional with independent flow rate valve
Seat F Jets.....	2 Jacuzzi® PowerPro® NX2, 3 Jacuzzi® PowerPro® MX
Footwell (G).....	8 Jacuzzi® PowerPro® FX Mini, 1 Jacuzzi® PowerPro® FX
Massage Selectors	2
Air Controls.....	4, On/Off rocker switch air controller
Water Management System.....	Two 60 ft² Filter cartridges; filter 1 on 8-hour circulation pump; filter 2 on jets pump 1; Factory installed ClearRay Active Oxygen® System; Optional True Water® System
Export (50 Hz):.....	N/A
LED Lighting	One underwater prolite with 4 color modes, one colored waterfall light, cup holders, 2 HYDROSOOTHE pillow lights, and exterior lights
ProFinish™ Cabinet Colors.....	Modern Hardwood, Brushed Gray, and Smoked Ebony
Acrylic Colors	Platinum, Silver Pearl, Morning Mist, Midnight, Canyon, Monaco (while quantities last)
Headrests	4
Waterfalls	One independent flow rate (on or off) adjustment; powered by the circulation pump
Heater:.....	North America (60 Hz): 5.5 kW, High Flow
Export (50 Hz):	N/A
Electrical Requirements:	North America (60 Hz): 240 VAC@40A, 50A, or 60A
Export (50 Hz):.....	N/A
Warranty*.....	North America (60 Hz): 10 Years Shell, 7 Years Shell Surface, 5 Years for Plumbing Component Leaks, 5 Years Equipment and Controls, 5 Years Cabinet, 2 Years Jets, 2 Years Lights, 1 Year Stereo;
Export (50 Hz):.....	N/A
Special Features (Standard).....	SmartTub® Module
Special Features (Optional).....	2 IR Therapy Lights
Audio System (Optional).....	BLUEWAVE® Spa Stereo System (Bluetooth/Aux compatible) with four speakers and a subwoofer



Shown with the optional IR Therapy Lights

Jacuzzi J-385

Operation/Seat Depths



51 Total Jets



Spa Operation Subject to Change without Notice

Seat Depths

A = 26.50" (67.31 cm)
B = 25.00" (63.50 cm)
C = 26.75" (67.95 cm)
D = 23.25" (59.06 cm)
E = 28.25" (71.76 cm)

F = 27.13" (68.90 cm)
G = 17.00" (43.18 cm)
H = 33.25" (84.46 cm)


Listed dimensions
represent distance
from top of acrylic to
lowest point in seat.
Tolerance $\pm 0.5"$
(1.27 cm).



Dimensions/Specifications are Subject to Change Without Notice

Jacuzzi J-385


Dimensions




FRONT

Equipment Bay/Pump Access
ClearRay Active Oxygen,
Optional BLUEWAVE,
and Optional SmartTub Module
behind skirt panels

FRONT/BACK VIEW
Tolerance: $\pm 0.5"$ (1.27 cm)




LEFT SIDE VIEW
Tolerance: $\pm 0.5"$ (1.27 cm)



STOP

IMPORTANT! Always measure each hot tub for exact dimensions BEFORE designing its foundational support and/or decking.

STOP



Important Panel Details

NOTE: Over time the panel(s) may bow, this is considered normal. The panels will straighten out when reinstalled into the mounting channel. Place one end of the panel into the channel first then flatten the panel and insert the other end.

Dimensions/specifications subject to change without notice. Tolerance $\pm 0.5"$ (1.27 cm)